



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED27T5H048GC850 27W Led T5HO 48" 50K GLS 3400LM *Keystone Technologies*

Catalog Number	LED27T5H048GC850
Manufacturer	Keystone Technologies
Description	Linear Fluorescent Led Lamp, Linear, Instant Start Type; 45.2 Inch; UI (Canada and Us), UI, NSF/Ansi, Etl Approval; Food Equipment, Splash Zone, Dry and Damp Location Application; 0.69 Inch Diameter; 27 Watt Wattage; Led Lamp
Weight per unit	0.4600 (lbs/each)
Product Category	20160824180628

Features

Beam Spread Angle	240 Degree
Glass Finish	FROSTED
Intensity	3400 Lumen
Item	LED Lamp
Wattage	27 Watt

Material, Color, and Finish

Base Type	G5 Miniature 2-Pin
Color Rendering Index	80 A
Color Temperature in Kelvin	5000

Dimensions and Weight

Diameter	0.69 Inch
Length	45.2 Inch

Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; System Wattage 30 Watt; Efficacy 125 Lumen per Watt; Visible Light Area 325 Degree; Temperature -20 to 45 Deg C
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	27W LED T5HO 48" 50K GLS 3400LM
Long Description	LINEAR FLUORESCENT LED LAMP, LINEAR, INSTANT START TYPE; 45.2 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL APPROVAL; FOOD EQUIPMENT, SPLASH ZONE, DRY AND DAMP LOCATION APPLICATION; 0.69 INCH DIAMETER; 27 WATT WATTAGE; LED LAMP

Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-LED27T5HO-48GC-850-S
Model	800



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Linear, Instant Start

Packaging

Carton	1
Package	40
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Food Equipment, Splash Zone, Dry and Damp Location
Approval	UL (Canada and US), UL, NSF/ANSI, ETL