



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED17T8L48FG841B *Delisted* 17W Led T8 48" 41K DBL 120-277V

Sylvania-Ledvance

| | |
|------------------|---|
| Catalog Number | LED17T8L48FG841B |
| Manufacturer | Sylvania-Ledvance |
| Description | OBSL48/FG/841/BFG2 4 FT, Ledlescent Ballast Free Led T8, Frosted Glass, 17W, 120 277V, 82 Cri, 2200 Lumens, 4100K CCT, 50000 Life |
| Weight per unit | 0.6712 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|--------------|-------------------|
| average life | 50000 |
| Base | G13 |
| Lamp Type | LED T8 |
| lumens | 2,200 |
| Shape | T8 |
| Voltage | 120.00 - 277.00 V |
| Wattage | 17.00 |

Material, Color, and Finish

| | |
|-----------------------------|--------------------|
| color rendering index (cri) | 82 |
| Style | Tube, double-ended |

Dimensions and Weight

| | |
|------|------|
| Size | 1.02 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | *DELISTED* 17W LED T8 48" 41K DBL 120-277V |
| extra long description | SYL LED17T8/L48/FG/841/BF/75026 LED |
| Long Description | OBSL48/FG/841/BFG2 4 ft, LEDlescent Ballast free LED T8, frosted glass, 17W, 120 277V, 82 CRI, 2200 Lumens, 4100K CCT, 50000 life |
| Product Type | LED17T8L48FG841BF 25/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135750267 |
| Manufacturers Part Number | LED17T8/L48/FG/841/BF/75026 |
| UPC | 046135750267 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.6712 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|