



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED4.5G25CLDIM92 LED4.5G25CLDIM927CECGLR 6 *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | LED4.5G25CLDIM92 |
| Manufacturer | Sylvania-Ledvance |
| Description | OBS40180 Led G25, 4.5W, Dimmable, 90CRI, 350 Lumen, 2700K, 15000 Life |
| Weight per unit | 0.2296 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|------------|
| average life | 15000 |
| Base | E26 Medium |
| dimmable | Yes |
| Lamp Type | LED G25 |
| lumens | 350 |
| Shape | G25 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 4.50 |

Material, Color, and Finish

| | |
|-----------------------------|-------|
| color rendering index (cri) | 90 |
| color temperature | 2700 |
| Style | GLOBE |

Dimensions and Weight

| | |
|------|------|
| Size | 3.15 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | LED4.5G25CLDIM927CECGLR 6 |
| extra long description | SYL LED4.5G25/CL/DIM/927/CEC/GL/RP/ |
| Long Description | OBS40180 LED G25, 4.5W, Dimmable, 90CRI, 350 Lumen, 2700K, 15000 life |
| Product Type | LED4.5G25CLDIM927CECGLR 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135401800 |
| Manufacturers Part Number | LED4.5G25/CL/DIM/927/CEC/GL/RP |
| sub brand | ULTRA HD |
| UPC | 046135401800 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED DECORATIVE C, CA, F, G SHAPE LAMPS |
|----------------------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.2296 |

Uses, Certifications, and Standards

| | |
|----------|-------|
| standard | cULus |
|----------|-------|