



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED6.5ST19DIM822 6.5W Led VNTG ST19 22K 650LM *Sylvania-Ledvance*

| | |
|------------------|--|
| Catalog Number | LED6.5ST19DIM822 |
| Manufacturer | Sylvania-Ledvance |
| Description | Led ST19, 7W, Dimmable, 80CRI, 590 Lumen, 2175K, 15000 Life, E26 Medium Base, Amber Finish |
| Weight per unit | 0.3817 (lbs/each) |
| Product Category | Led Decorative C, Ca, F, G Sha |

Features

| | |
|----------------|------------|
| average life | 15000 |
| Base | E26 Medium |
| dimmable | Yes |
| Lamp Type | LED ST19 |
| lumens | 590 |
| Shape | ST19 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 6.50 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| color rendering index (cri) | 80 |
| color temperature | 2175 |

Dimensions and Weight

| | |
|------|------|
| Size | 2.52 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 6.5W LED VNTG ST19 22K 650LM |
| extra long description | SYL LED6.5ST19/DIM/822/VIN/G2/RP/75 |
| Long Description | LED ST19, 7W, Dimmable, 80CRI, 590 Lumen, 2175K, 15000 Life, E26 Medium Base, AMBER Finish |
| Product Type | LED6.5ST19DIM822VING2RP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Ledvance LLC |
| GTIN | 00046135753534 |
| Manufacturers Part Number | LED6.5ST19/DIM/822/VIN/G2/RP/7 |
| UPC | 046135753534 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED DECORATIVE C, CA, F, G SHAPE LAMPS |
|----------------------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.3817 |

Uses, Certifications, and Standards

| | |
|----------|-------|
| standard | cULus |
|----------|-------|