



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7.5T824G8CSJX 7W Led T8 24" 3K/35/4K/5K/65K Combo (Type A-B)

Keystone Technologies

Catalog Number	LED7.5T824G8CSJX
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, 1150 Lumen, Glass Construction, 2FT, Color Select 3000/3500/4000/5000K/6500K, Ballast Compatible & 120-277V Line Voltage Compatible (Single or Double Ended Wiring), Combo Drive X3
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V OR Ballast Dependent
ip rating	N/A
lumens	1150
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	7W LED T8 24" 3K/35/4K/5K/65K COMBO (TYPE A-B)
extra long description	Key KT-LED7.5T8-24G-8CSJ-X3 7W LED
Long Description	7W LED T8 Tube, 1150 lumen, Glass Construction, 2ft, Color Select 3000/3500/4000/5000K/6500k, Ballast Compatible & 120-277V Line Voltage Compatible (Single OR Double Ended Wiring), Combo Drive X3
Product Type	7W Led T8 Tube, 1150 Lumen, Glass Construction, 2FT, Color S



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654156125
Manufacturers Part Number	KT-LED7.5T8-24G-8CSJ-X3
UPC	843654156125

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.4

Uses, Certifications, and Standards

Energy Star	N
-------------	---