



A simple upgrade to your existing high bay fixtures that can be done today!



HIGH BAY RETROFITS

Ideal for use in:

- Large retail spaces
- Industrial spaces
- Auditoriums
- Gymnasiums
- Warehouses
- Factories

Retrofits into most popular high bay fixtures



100W
LED-8036M

Replaces up to
250W



140W
LED-8030M*

Replaces up to
400W

**Aims light upward,
sideways, and down**



140W
LED-8032M*

Replaces up to
400W

**Total downlight
for ultra-high ceilings**

Ask about our metal halide ballast compatible models

* Design Patent
D723,194

* Design Patent
29/519,210

DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
LED-8036M 100W HIGH BAY LIGHTING	LED-8036M40-A	LED-8036M40-A (120V) LED-8036M40C-A (347V)	Up to 10902	100W	250W	EX39	4000K	✓	✓	7.6" x 7.9"
	LED-8036M57-A	LED-8036M57-A (120V) LED-8036M57C-A (347V)	Up to 11015	100W	250W	EX39	5700K	✓	✓	7.6" x 7.9"
LED-8030M 140W HIGH BAY LIGHTING	LED-8030M40-A	LED-8030M40-A (120V) LED-8030M40C-A (347V)	Up to 15763	140W	400W	EX39	4000K	✓	✓	9.2" x 9.1"
	LED-8030M57A	LED-8030M57-A (120V) LED-8030M57C-A (347V)	Up to 15966	140W	400W	EX39	5700K	✓	✓	9.2" x 9.1"
LED-8032M 140W HIGH BAY LIGHTING	LED-8032M40-A	LED-8032M40-A (120V) LED-8032M40C-A (347V)	Up to 16668	140W	400W	EX39	4000K	✓	✓	9.4" x 9.1"
	LED-8032M57-A	LED-8032M57-A (120V) LED-8032M57C-A (347V)	Up to 16923	140W	400W	EX39	5700K	✓	✓	9.4" x 9.1"
LED-8034M 150W HIGH BAY LIGHTING	LED-8034M50	LED-8034M50 (120V)	Up to 19344	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
	LED-8034M50-HV (480V)	LED-8034M50-HV (347V)	Up to 19022	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
LED-8050M 300W HIGH BAY LIGHTING	LED-8050M50	LED-8050M50 (120V)	Up to 34153	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"
	LED-8050M50-HV (480V)	LED-8050M50-HV (347V)	Up to 33533	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"

VOLTAGE:  120-277VAC  347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY



A simple upgrade to your existing high bay fixtures that can be done today!



HIGH BAY RETROFITS

Ideal for use in:

- Large retail spaces
- Industrial spaces
- Auditoriums
- Gymnasiums
- Warehouses
- Factories

Retrofits into most popular high bay fixtures



100W
LED-8036M

Replaces up to
250W



140W
LED-8030M*

Replaces up to
400W



140W
LED-8032M*

Replaces up to
400W

**Aims light upward,
sideways, and down**

**Total downlight
for ultra-high ceilings**

Ask about our metal halide ballast compatible models

* Design Patent
D723,194

* Design Patent
29/519,210

DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
LED-8036M 100W HIGH BAY LIGHTING	LED-8036M40-A	LED-8036M40-A (120V) LED-8036M40C-A (347V)	Up to 10902	100W	250W	EX39	4000K	✓	✓	7.6" x 7.9"
	LED-8036M57-A	LED-8036M57-A (120V) LED-8036M57C-A (347V)	Up to 11015	100W	250W	EX39	5700K	✓	✓	7.6" x 7.9"
LED-8030M 140W HIGH BAY LIGHTING	LED-8030M40-A	LED-8030M40-A (120V) LED-8030M40C-A (347V)	Up to 15763	140W	400W	EX39	4000K	✓	✓	9.2" x 9.1"
	LED-8030M57A	LED-8030M57-A (120V) LED-8030M57C-A (347V)	Up to 15966	140W	400W	EX39	5700K	✓	✓	9.2" x 9.1"
LED-8032M 140W HIGH BAY LIGHTING	LED-8032M40-A	LED-8032M40-A (120V) LED-8032M40C-A (347V)	Up to 16668	140W	400W	EX39	4000K	✓	✓	9.4" x 9.1"
	LED-8032M57-A	LED-8032M57-A (120V) LED-8032M57C-A (347V)	Up to 16923	140W	400W	EX39	5700K	✓	✓	9.4" x 9.1"
LED-8034M 150W HIGH BAY LIGHTING	LED-8034M50	LED-8034M50 (120V)	Up to 19344	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
	LED-8034M50-HV (480V)	LED-8034M50-HV (347V)	Up to 19022	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
LED-8050M 300W HIGH BAY LIGHTING	LED-8050M50	LED-8050M50 (120V)	Up to 34153	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"
	LED-8050M50-HV (480V)	LED-8050M50-HV (347V)	Up to 33533	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"

VOLTAGE:  120-277VAC  347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY