

Eaton LKS-100

Catalog Number: LKS-100

Eaton Bussmann series LKS fuse link, 600V, 100A, Class H, K5



General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-100
UPC	EAN
051712141000	5027590127578
Product Length/Depth	Product Height
0.625 in	5.125 in
Product Width	Product Weight
0.688 in	0.028 lb
Warranty	Compliances
Not Applicable	RoHS Compliant

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

100 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Catalogs

Bussmann series complete full line catalog no. 1007

[LKS-100~SUPER LAG RENEWABLE LINK](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-100](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton LKS-100

Catalog Number: LKS-100

Eaton Bussmann series LKS fuse link, 600V, 100A, Class H, K5



General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-100
UPC	EAN
051712141000	5027590127578
Product Length/Depth	Product Height
0.625 in	5.125 in
Product Width	Product Weight
0.688 in	0.028 lb
Warranty	Compliances
Not Applicable	RoHS Compliant

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

100 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Catalogs

Bussmann series complete full line catalog no. 1007

[LKS-100~SUPER LAG RENEWABLE LINK](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-100](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)