

Specifications

Photo is representative

Eaton LL47 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LL shape, 1-1/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LL47 SA
UPC	782274524818
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	3.19 in
PRODUCT WIDTH	2.31 in
PRODUCT WEIGHT	0.93 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS [IF 964 - Conduit Body Wire Pulling](#)
[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Condulet Form 7 Industrial Grade Conduit Bodies](#)
[Eaton Specification Sheet - LL47 SA](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)
[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Product specifications

SHAPE	LL
TRADE SIZE	1-1/4"
MATERIAL	Copper-free aluminum



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton LL47 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LL shape, 1-1/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LL47 SA
UPC	782274524818
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	3.19 in
PRODUCT WIDTH	2.31 in
PRODUCT WEIGHT	0.93 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS [IF 964 - Conduit Body Wire Pulling](#)
[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Condulet Form 7 Industrial Grade Conduit Bodies](#)
[Eaton Specification Sheet - LL47 SA](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)
[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Product specifications

SHAPE	LL
TRADE SIZE	1-1/4"
MATERIAL	Copper-free aluminum



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

