

Eaton LL87 SA

Catalog Number: LL87 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LL shape, 3"

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LL87 SA
	UPC
	782274364834
Product Length/Depth	Product Height
10.5 in	5.75 in
Product Width	Product Weight
4.38 in	3.95 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

LL

Trade size

3"

Material

Copper-free aluminum

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - LL87 SA](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton LL87 SA

Catalog Number: LL87 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LL shape, 3"

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LL87 SA
	UPC
	782274364834
Product Length/Depth	Product Height
10.5 in	5.75 in
Product Width	Product Weight
4.38 in	3.95 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

LL

Trade size

3"

Material

Copper-free aluminum

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - LL87 SA](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)