



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LPX7 Led, White, Universal Face, Red Letters, S *Cooper Lighting Solutions*

| | |
|------------------|---|
| Catalog Number | LPX7 |
| Manufacturer | Cooper Lighting Solutions |
| Description | Led, White Housing, Universal Face, Red and Green Letters, Self-Powered |
| Weight per unit | 3.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------------|
| amperage rating | 0.07A |
| battery | Nickel Cadmium |
| Fixture Type | Exit Light |
| Lamp Type | LED |
| lumens | N/A |
| Material | Polycarbonate |
| Number of Lamps | 1 |
| Voltage Rating | 120 / 277V |
| Wattage | 0.98W/1.03W |

Dimensions and Weight

| | |
|------|---|
| Size | 14.0 IN Length 8.063 IN Width 2.813 IN Height |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | LED, WHITE, UNIVERSAL FACE, RED LETTERS, S |
| extra long description | CLS LPX7 EXIT,WH P HOUS,UNV, R N G, |
| Long Description | LED, White Housing, Universal Face, Red and Green Letters, Self-Powered |
| Product Type | Exit, WH P Hous, Unv, R N G, W Bat |
| Special Features | Dual voltage input 120/277 VAC |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton Lighting |
| GTIN | 00080083532773 |
| Manufacturers Part Number | LPX7 |
| UPC | 080083532773 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Emergency & Exit Lighting |
| Type | Exit Signs |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 3 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | lighting |
| Mounting | Ceiling/Wall Mount |
| standard | NFPA 101 Compliant; NEC Class I; OSHA Compliant; UL Listed - Damp Location |