



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LR35 1" Alu LR SR5 Conduit Body

Crouse-Hinds

Catalog Number	LR35
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Body, Epoxy Powder Painted (Body);Natural (Gasket), 1 In Trade Size, Threaded/Set Screw Connection, 12.2 Cu.In Capacity, 90 ° Angle, 1 In Hub Size, 5.94 In Length, 2.51 In Width, 1.9 In Height, 0.51 LB/Ea
Weight per unit	0.5100 (lbs/each)
Product Category	Alum

Features

connection	Threaded / Set Screw
dimensions	5.9400 IN X 1.9000 IN X 2.5100 IN
Form	Series 5

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Height	1.90
Hub Size	1 in
Width	2.51

Descriptions

Description	1" ALU LR SR5 CONDUIT BODY
extra long description	MIDWEST LR35 1 RGD LR COND BODY AL
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer

Manufacturer Information

Brand	Eaton
GTIN	00784564140135
UPC	784564140135

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 5

Weight Per each 0.51

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure Condulet

Mounting Conduit

standard UL, cUL