

# Specifications

## Eaton LR37



Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1"

Photo is representative



### General specifications

|                                 |   |
|---------------------------------|---|
| <b>PRODUCT NAME</b>             | Eaton Crouse-Hinds series<br>Condulet Form 7 conduit<br>outlet body |
| <b>CATALOG NUMBER</b>           | LR37  |
| <b>UPC</b>                      | 782274528403  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 6 in  |
| <b>PRODUCT HEIGHT</b>           | 2.75 in   |
| <b>PRODUCT WIDTH</b>            | 1.88 in   |
| <b>PRODUCT WEIGHT</b>           | 1.72 lb   |

## Certifications and compliances

|                     |                                  |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE      | NEC/CEC                          |
| NEMA RATING         | 12                               |

## Resources

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - LR37](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

## Product specifications

|            |                    |
|------------|--------------------|
| SHAPE      | LR                 |
| TRADE SIZE | 1"                 |
| MATERIAL   | Feraloy iron alloy |



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton LR37



Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1"

Photo is representative



### General specifications

|                                 |   |
|---------------------------------|---|
| <b>PRODUCT NAME</b>             | Eaton Crouse-Hinds series<br>Condulet Form 7 conduit<br>outlet body |
| <b>CATALOG NUMBER</b>           | LR37  |
| <b>UPC</b>                      | 782274528403  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 6 in  |
| <b>PRODUCT HEIGHT</b>           | 2.75 in   |
| <b>PRODUCT WIDTH</b>            | 1.88 in   |
| <b>PRODUCT WEIGHT</b>           | 1.72 lb   |

## Certifications and compliances

|                            |                                  |
|----------------------------|----------------------------------|
| <b>AREA CLASSIFICATION</b> | Ordinary/Non-Hazardous Locations |
| <b>STANDARDS TYPE</b>      | NEC/CEC                          |
| <b>NEMA RATING</b>         | 12                               |

## Resources

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - LR37](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Product specifications

|                   |                    |
|-------------------|--------------------|
| <b>SHAPE</b>      | LR                 |
| <b>TRADE SIZE</b> | 1"                 |
| <b>MATERIAL</b>   | Feraloy iron alloy |



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

