



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LSF120SFPC 50/70/90/120W Led Flood 3K/4K/5K Slipfitter Mount

Cooper Lighting Solutions

Catalog Number	LSF120SFPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 Cri, 120-347V, 50-60 HZ, Selectable Lumens 9000-12, 000-15, 000-20, 000 / 50-70-90-120W, Selectable Dusk-to-Dawn Button-Type Photocontrol, Slipfitter
Weight per unit	12.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.345A @347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	9000-12000-15000-20000
Voltage Rating	120-347V

Dimensions and Weight

Size	21.5 IN Length 12.6 IN Width 4.13 IN Height
------	---

Descriptions

Description	50/70/90/120W LED FLOOD 3K/4K/5K SLIPFITTER MOUNT
extra long description	CLS LSF120-SF-PC CCT SELECT FLOOD,
Long Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 CRI, 120-347V, 50-60 Hz, Selectable Lumens 9000-12,000-15,000-20,000 / 50-70-90-120W, Selectable Dusk-to-Dawn Button-type photocontrol, Slipfitter
Product Type	CCT Select Flood, 120W, SF, PC
Special Features	Available in 3 housing sizes and multiple lumen packages

Manufacturer Information

Brand	LUMARK
GTIN	00080083267743
Manufacturers Part Number	LSF120-SF-PC
UPC	080083267743

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	12.02



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	SLIPFITTER
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant