



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LSF65KNYKPC 25/35/45/65W Led Flood 3K/4K/5K Yoke & KNKL MNT *Cooper Lighting Solutions*

Catalog Number	LSF65KNYKPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 5000-6500-8000-10, 000, 65W, 70 Cri, 120-347V, 50-60 HZ, Dusk-to-Dawn Via Button-Type Photocontrol
Weight per unit	3.8 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.18A at 347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	10000
Voltage Rating	120-347V

Dimensions and Weight

Size	0.0 IN Length 0.0 IN Width 0.0 IN Height
------	--

Descriptions

Description	25/35/45/65W LED FLOOD 3K/4K/5K YOKE & KNKL MNT
extra long description	CLS LSF65-KNYK-PC CCT SELECT FLOOD,
Long Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 5000-6500-8000-10,000, 65W, 70 CRI, 120-347V, 50-60 Hz, Dusk-to-Dawn via Button-type photocontrol
Product Type	CCT Select Flood, 65W, KNC & Yoke, PC
Special Features	Available in selectable CCT and selectable lumens

Manufacturer Information

Brand	LUMARK INDOOR
GTIN	00080083305254
Manufacturers Part Number	LSF65-KNYK-PC
UPC	080083305254

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	3.83



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Knuckle/Yoke
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant