



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LR69 2" Alu LR MK9 Conduit Body

*Crouse-Hinds*

Catalog Number	LR69
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, LR Shape, 2"
Weight per unit	2.2 (lbs/each)
Product Category	Alum

### Features

dimensions	10.0900 IN X 3.4400 IN X 4.2000 IN
------------	------------------------------------

### Material, Color, and Finish

Finish	Untreated
--------	-----------

### Dimensions and Weight

Height	3-7/16
Hub Size	2 in
Length	10-1/32
Width	4-1/8

### Descriptions

Description	2" ALU LR MK9 CONDUIT BODY
extra long description	CRS-H LR69 2 LR MARK 9 CNDT BODY
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, LR shape, 2"
Product Type	2 LR Mark 9 CNDT Body

### Manufacturer Information

Brand	Eaton
GTIN	00782274529509
Manufacturers Part Number	LR69
UPC	782274529509

### Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	2
Weight Per each	2.18

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D