



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT114UL 1-1/4" Ua Sealtite Conduit, Bonded UI 50' *Southwire Company*

Catalog Number	LT114UL
Manufacturer	Southwire Company
Description	TITAN2 Type UI LFMC Is Manufactured With A Spiral Wound Strip Of Heavy Gauge Corrosion-Resistant Hot-Dipped Galvanized Steel. For 3/8" Through 1-1/4" Trade Sizes The Core Is Constructed With A Square Locked Steel Strip With An Integral Copperbonding Strip Enclosed Within The Steel Convolutions. For 1-1/2" Through 4" Trade Sizes The Core Is Constructed With A Fully Interlocked Steel Strip. A Rugged Flame Retardant Flexible PVC Jacket Is Extruded Over The Steel Core. The Grey Jacket Resists Oils Mild
Weight per unit	0.6600 (lbs/each)
Product Category	Conduit & Raceways

Features

outside diameter	1645
------------------	------

Dimensions and Weight

Length	50
--------	----

Descriptions

extra long description	SWC 55093305 Titan2 Type UL Liquidt
Long Description	Titan2 Type UL LFMC is manufactured with a spiral wound strip of heavy gauge corrosion-resistant hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes the core is constructed with a square locked steel strip with an integral copperbonding strip enclosed within the steel convolutions. For 1-1/2" through 4" trade sizes the core is constructed with a fully interlocked steel strip. A rugged flame retardant flexible PVC jacket is extruded over the steel core. The grey jacket resists oils mild
Product Type	TITAN2 Type UI Liquidtight Flexible Metal Conduit

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886042386
Manufacturers Part Number	55093305
UPC	032886042386

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 1 1/4

Availability

Status Inactive

Packaging

Carton 50

Weight Per each 0.66