



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LR888 3" LR FM8 Conduit Body

*Crouse-Hinds*

Catalog Number	LR888
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 8 Conduit Outlet Body, Feraloy Iron Alloy, LR Shape, 3"
Weight per unit	15.4 (lbs/each)
Product Category	Bodies & Covers

### Features

dimensions	13.9400 IN X 4.8100 IN X 6.6900 IN
Form	Form 8

### Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

### Dimensions and Weight

Height	4-13/16
Hub Size	3 in
Length	13-15/16
Width	6-11/16

### Descriptions

Description	3" LR FM8 CONDUIT BODY
extra long description	CRS-H LR888 3 LR FORM 8 CNDT BODY
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 8 bodies are offered in seven different shapes to provide the most flexible offering on the market. Form 8 Condulet outlet bodies provide more room for heavier conductors. Many shapes and sizes are available for rigid threaded conduit. Two cover screws on all body sizes provide tight
Long Description	Eaton Crouse-Hinds series Condulet Form 8 conduit outlet body, Feraloy iron alloy, LR shape, 3"
Product Type	3 LR Form 8 CNDT Body

### Manufacturer Information

Brand	Eaton
GTIN	00782274530604
Manufacturers Part Number	LR888
UPC	782274530604



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body

## Packaging

Carton	1
Weight Per each	15.38

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D