



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LTB25045 2-1/2" 45D LT Conn *Crouse-Hinds*

Catalog Number	LTB25045
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Liquidator Liquidtight Connector, FMC, 45° Angle, Insulated, Malleable Iron, 2-1/2"
Weight per unit	5.4 (lbs/each)
Product Category	Liquid Tight Fittings

Features

connection	Threaded
dimensions	8.3100 IN X 4.0000 IN X 8.3100 IN
installation type	THREADED

Material, Color, and Finish

Color	MALLEABLE IRON
-------	----------------

Descriptions

Description	2-1/2" 45D LT CONN
extra long description	MIDWEST LTB25045 2 1/2 LT 45 DEGREE
Features	Liquidtight fittings from Eaton's Crouse-Hinds Division are designed to protect conductors from mechanical damage due to vibration and movement while sealing out cutting oils, coolants, water, and dust. Typical applications include the wiring of machine tools, motors, transformers, food processing equipment, robotics, air conditioning units and illuminated signs. To meet any customer preference, Crouse-Hinds series liquidtight fittings are available in a variety sizes, configurations and materials, inclu
Long Description	Eaton Crouse-Hinds series Liquidator liquidtight connector, FMC, 45° angle, Insulated, Malleable iron, 2-1/2"
Product Type	2 1/2 LT 45 Degree Conn Insulated

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564462503
Manufacturers Part Number	LTB25045
UPC	784564462503

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Liquidtight connector

Trade Size

Trade Size	2 1/2 in
------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	5.4

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 467, UL 514B, CSA C22.105