



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LTC100TB 1" LT NM Flex CNDT

*Abb Installation Products, Inc*

Catalog Number	LTC100TB
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, UI Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings
Weight per unit	0.3031 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Inside Diameter	1.0394
outside diameter	1.315
Voltage Rating	600 V

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Length	1200.7874
--------	-----------

### Descriptions

Description	1" LT NM FLEX CNDT
extra long description	ABB LTC100-TB 1IN LT TYPE B COND PV
Long Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings
Product Type	1IN LT Type B Cond PVC BLK
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily

### Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210789569
Manufacturers Part Number	LTC100-TB
UPC	786210789569

### Taxonomies, Classifications, and Categories

Category Description	PVC & ENT
Type	Liquidtight Flexible Non-Metallic Conduit



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 1 in

## Packaging

Carton ..... 100

Weight Per foot ..... 0.3031

## Uses, Certifications, and Standards

Application ..... Machine Tools, Motor Hookups, Food Processing Equipment,  
Extensions from Wire Ways, and Sensor and Micro Switch Wiring  
Found In Control Consoles

standard ..... UL E95745, CSA