



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LTC150TB 1-1/2" LT BLK Flex PVC CNDT

Abb Installation Products, Inc

Catalog Number	LTC150TB
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1-1/2 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, Ul Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings
Weight per unit	0.5200 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Inside Diameter	1.57480
outside diameter	1.90160
Voltage Rating	600 V

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	0.59840
--------	---------

Descriptions

Description	1-1/2" LT BLK FLEX PVC CNDT
extra long description	ABB LTC150-TB 1-1/2IN LT TYPE B CON
Long Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1-1/2 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings
Product Type	1-1/2IN LT Type B Cond PVC BLK
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily

Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210789583
Manufacturers Part Number	LTC150-TB
UPC	786210789583

Taxonomies, Classifications, and Categories

Type	Liquidtight Flexible Non-Metallic Conduit
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 1-1/2 in

Availability

minimum qty 50

Packaging

Carton 50

Weight Per foot 0.52

Uses, Certifications, and Standards

Application Machine Tools, Motor Hookups, Food Processing Equipment,
Extensions from Wire Ways, and Sensor and Micro Switch Wiring
Found In Control Consoles

standard UL E95745, CSA