



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DLHRK11230RP Red Ext III Mom PB 1NO/1NC 85 - 264VAC Led LGND PL Eaton Corp

Catalog Number	M22DLHRK11230RP
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Device, 22.5 MM, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, Nema 4X, 13, 85-264V
Weight per unit	0.1100 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Button, Extended
Contact Configuration	1 NO-1 NC
dimensions	1.4600 IN X 1.1800 IN X 3.4500 IN
Voltage Rating	85-264 V

Dimensions and Weight

Depth	1.46
Height	3.45
Size	22.5 mm
Width	1.18

Descriptions

Description	RED EXT ILL MOM PB 1NO/1NC 85 - 264VAC LED LGND PL
extra long description	ETN M22-DLH-R-K11-230R-P NEMA 4X, 1
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Complete Device, 22.5 mm, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, NEMA 4X, 13, 85-264V
Product Type	Nema 4X, 13, 85-264V
Special Features	M22 series

Manufacturer Information

Brand	Eaton
GTIN	00786685382555
Manufacturers Part Number	M22-DLH-R-K11-230R-P
Model	Modular pushbutton
UPC	786685382555



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Modular pushbutton

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CSA Certified,CCC Marked,Lloyd's Register Certified,CE Marked,GoST-R,Bureau Veritas