



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU70HECO 70W ED23.5 High Pressure Sodium Clear Mogul Base

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | LU70HECO |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Ecolux®, 85368, 70 WTT, 1.6 Amp, 6400 LM, 1900 KV, 22 Cri, Mogul Screw (E39) Base, 24000 HR Average Life |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | Hid High Pressure Sodium Lamps |

Features

| | |
|-----------------|-------|
| amperage rating | 1.6 |
| average life | 24000 |
| Base | E39 |
| lumens | 6400 |
| Wattage | 70 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Clear |
| color rendering index (cri) | 22.0 |
| color temperature | 1900.0 |
| Finish | Clear |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|---|
| Description | 70W ED23.5 HIGH PRESSURE SODIUM CLEAR MOGUL BASE |
| extra long description | GEL LU70/H/ECO 85368 LUCALOX |
| Long Description | GE Ecolux®, 85368, 70 WTT, 1.6 AMP, 6400 LM, 1900 KV, 22 CRI, Mogul Screw (E39) Base, 24000 HR Average Life |
| Product Type | 85368 Lucalox |
| Special Features | 7.75IN Length |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168853682 |
| Manufacturers Part Number | LU70/H/ECO |
| UPC | 043168853682 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------|
| Category Description | SODIUM |
|----------------------|--------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.35 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Universal burning position