

More on reverse!

Non-metallic Combination Boxes!

LVD2 Power & Low Voltage Combo Box for New Construction




LVD2
Non-metallic,
Power and
Low Voltage
Combo Box

Patent pending


Easy installation – Nail or screw the LVD2 box to a wood or metal stud

Installing power and low voltage boxes? Try Arlington's non-metallic Combination Boxes.

LVD2 is the best way to install power and phone/cable outlets together, in one neat location in *new construction*.



Why accept this... when you can have a neat installation, like this.



Just nail the LVD2 to a wood stud, or screw

onto metal studs. Installation is fast and easy!

The low voltage side, for low voltage/Class 2 wiring includes combo 1/2" and 3/4" KOs for raceway.

LVD2 protects cable from damage – and it's the sturdiest box of its kind.



- UL Listed
- Competitively priced
- Ships ready to install with (2) nails in place

Catalog #	UPC/DCI/NAED Mfg. #01 8997	Unit/Std Pkg
LVD2	10957	25

Combination non-metallic, power & low voltage **combo box** for new construction.

for New Construction

Optional Wall Plates...

- One-piece design saves time and money!
- Include coaxial cable connector and modular phone/cable wall jack
- Accept inexpensive standard receptacles



Back

Optional Wall Plates for LVD2, LVDR2

Catalog #	UPC/DCI/NAED Mfg. #01 8997	Color	Unit/Std Pkg
LVD2CI	10999	Ivory	25
LVD2CW	10997	White	25

OPTIONAL Wall plates for LVD2 and LVDR2 combo boxes



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Non-metallic Combination Boxes!

LVD2 on reverse!

LVDR2 Power & Low Voltage Combo Box for Existing Construction

Arlington's LVDR2 dual voltage, 2-gang box for retrofit work also installs power *and* low voltage outlets together in one neat location.

This 17 cu. inch box delivers a secure installation and adjusts to fit walls from 1/4" to 1-1/2" thick in existing construction.

As the mounting screws are tightened, the wings flip up, locking the box firmly in place.


The low voltage side, for low voltage/Class 2 wiring includes combo 1/2" and 3/4" KOs for raceway.

- UL Listed
- Competitively priced
- Ships with installed NM cable connector

Optional Wall Plates for LVDR2, LVD2 save time and money! Available in white or ivory. (See front of sheet for details).



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com




LVDR2
Non-metallic, Power & Low Voltage
Combo Box



Catalog #	UPC/DCI/NAED Mfg. #01 8997	Unit/Std Pkg
LVDR2	01000	25
2-gang, non-metallic, power & low voltage combo box for existing work.		

for Existing Construction

Distributed by



More on reverse!

Non-metallic Combination Boxes!

LVD2 Power & Low Voltage Combo Box for New Construction




LVD2
Non-metallic,
Power and
Low Voltage
Combo Box

Patent pending


Easy installation – Nail or screw the LVD2 box to a wood or metal stud

Installing power and low voltage boxes? Try Arlington's non-metallic Combination Boxes.

LVD2 is the best way to install power and phone/cable outlets together, in one neat location in *new construction*.



Why accept this... when you can have a neat installation,



like this. Just nail the LVD2 to a wood stud, or screw

onto metal studs. Installation is fast and easy!

The low voltage side, for low voltage/Class 2 wiring includes combo 1/2" and 3/4" KOs for raceway.

LVD2 protects cable from damage – and it's the sturdiest box of its kind.



- UL Listed
- Competitively priced
- Ships ready to install with (2) nails in place


Catalog #	UPC/DCI/NAED Mfg. #01 8997	Unit/Std Pkg
LVD2	10957	25

Combination non-metallic, power & low voltage **combo box** for new construction.

for New Construction

Optional Wall Plates...

- One-piece design saves time and money!
- Include coaxial cable connector and modular phone/cable wall jack
- Accept inexpensive standard receptacles



Back

Optional Wall Plates for LVD2, LVDR2

Catalog #	UPC/DCI/NAED Mfg. #01 8997	Color	Unit/Std Pkg
LVD2CI	10999	Ivory	25
LVD2CW	10997	White	25

OPTIONAL Wall plates for LVD2 and LVDR2 combo boxes



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Non-metallic Combination Boxes!

LVD2 on reverse!

LVDR2 Power & Low Voltage Combo Box for Existing Construction

Arlington's LVDR2 dual voltage, 2-gang box for retrofit work also installs power *and* low voltage outlets together in one neat location.

This 17 cu. inch box delivers a secure installation and adjusts to fit walls from 1/4" to 1-1/2" thick in existing construction.

As the mounting screws are tightened, the wings flip up, locking the box firmly in place.


The low voltage side, for low voltage/Class 2 wiring includes combo 1/2" and 3/4" KOs for raceway.

- UL Listed
- Competitively priced
- Ships with installed NM cable connector


Optional Wall Plates for LVDR2, LVD2 save time and money! Available in white or ivory. (See front of sheet for details).



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com



LVDR2
Non-metallic, Power & Low Voltage
Combo Box



Catalog #	UPC/DCI/NAED Mfg. #01 8997	Unit/Std Pkg
LVDR2	01000	25
2-gang, non-metallic, power & low voltage combo box for existing work.		

for Existing Construction

Distributed by

