



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DB Non-III Mom PB Sil-BZL FLSH Blu

Eaton Corp

Catalog Number	M22DB
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMO-Titan Pushbutton, Blue Actuator, Silver Bezel, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13, 5, 000, 000 Operations, Momentary, 22.5 MM, Flush Pushbutton, M22
Weight per unit	1.0 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Blue
actuator	Flush, Button
dimensions	2.0000 IN X 2.0000 IN X 1.0000 IN
operating cycles	5 million

Dimensions and Weight

Depth	2
Height	1
Size	22.5 mm
Width	2

Descriptions

Description	NON-ILL MOM PB SIL-BZL FLSH BLU
extra long description	ETN M22-D-B NON-ILL MOM PB SIL-BZL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMO-Titan Pushbutton,Blue Actuator,Silver bezel,IP67, IP69K,Non-Illuminated,Flush mounting,NEMA 4X, 13,5,000,000 operations,Momentary,22.5 mm,Flush Pushbutton,M22
Product Type	Non-III Mom PB Sil-BZL FLSH Blu



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786685275970
Manufacturers Part Number	M22-D-B
Model	Modular pushbutton
UPC	786685275970

Taxonomies, Classifications, and Categories

Category Description	PUSHBUTTONS & CHIMES
Type	Modular pushbutton

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
Mounting	FLUSH
standard	CSA Certified, Lloyd's Register Certified, CCC Marked, Bureau Veritas, GoST-R, CE Marked