



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22XDSWRGYB FLSH Button 6-Pack For Non-III PB

Eaton Corp

Catalog Number	M22XDSWRGYB
Manufacturer	Eaton Corp
Description	Eaton M22 Pushbutton Button Plate, M22 Button Plate, 22.5 MM, Flush, Non-Illuminated, Button: Black, White, Red, Green, Yellow, Blue, IP67, IP69K, Nema 4X, 21
Weight per unit	0.0200 (lbs/each)
Product Category	Push Button Components

Features

dimensions	1.0000 IN X 1.0000 IN X 0.0100 IN
------------	-----------------------------------

Dimensions and Weight

Depth	1
Height	0.01
Size	22.5 mm
Width	1

Descriptions

Description	FLSH BUTTON 6-PACK FOR NON-ILL PB
extra long description	ETN M22-XD-SWRGYB FLSH BUTTON 6-PAC
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 pushbutton button plate, M22 Button Plate, 22.5 mm, Flush, Non-illuminated, Button: Black, white, red, green, yellow, blue, IP67, IP69K, NEMA 4X, 21
Product Type	FLSH Button 6-Pack For Non-III PB

Manufacturer Information

Brand	Eaton
GTIN	00786685273624
Manufacturers Part Number	M22-XD-SWRGYB
UPC	786685273624

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Pushbutton accessory



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	Lloyd's Register Certified, CSA Certified, CCC Marked, CE Marked, GoST-R, Bureau Veritas