



## M22DRXSRG Non-III MTN PB Sil-BZL FLSH Button 3-Pack

Eaton Corp

Catalog Number	M22DRXSRG
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMQ-Titan Pushbutton, Black, Red, Green Actuator, Silver Bezel, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13, 1, 000, 000 Operations, Maintained, 22.5 MM, Flush Pushbutton, M22
Weight per unit	0.0400 (lbs/each)
Product Category	Push Button Complete Assemblie

### Features

*comes w/ bk/rd/grn covers	Button*
action	Black, green, red
actuator	Flush, Button
operating cycles	1 million

### Dimensions and Weight

Depth	1.5
Height	1.25
Size	22.5 mm
Width	1.75

### Descriptions

Description	NON-ILL MTN PB SIL-BZL FLSH BUTTON 3-PACK
extra long description	ETN M22-DR-X-SRG NON-ILL MTN PB SIL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMQ-Titan Pushbutton,Black, Red, Green Actuator,Silver bezel,IP67, IP69K,Non-illuminated,Flush mounting,NEMA 4X, 13, 1,000,000 operations,Maintained,22.5 mm,Flush Pushbutton,M22
Product Type	Non-ILL MTN PB Sil-BZL FLSH Button 3pack



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 N Simon Sager Ave  
72761-0000, AR Siloam Springs  
Phone: 479-238-1561  
Fax: 479-238-1461

## Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685276465
Manufacturers Part Number	M22-DR-X-SRG
Model	Modular pushbutton
UPC	786685276465

## Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------

## Packaging

Carton	1
Weight Per each	0.04

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
Mounting	FLUSH
standard	Lloyd's Register Certified, CCC Marked, CSA Certified, CE Marked, Bureau Veritas, GOST-R