



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MAEL153MHIV Maestro 150W Led Multi Ivory

Lutron

Catalog Number	MAEL153MHIV
Manufacturer	Lutron
Description	Maestro Led+ Multiloc, Clamshell Ivory
Weight per unit	1.6 (lbs/each)
Product Category	Lighting Dimmers

### Features

Connection Type	Screw Terminal
insulation	Plastic
Poles	1
Switch Type	Tapswitch
Voltage Rating	120
Wattage	600

### Material, Color, and Finish

Color	Ivory
Finish	Gloss

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	MAESTRO 150W LED MULTI IVORY
extra long description	LUT MAEL-153MH-IV MAESTRO LED+ MULT

Features  
The Maestro LED+ dimmer switch provides optimal dimming performance of LED bulbs. This dimmer switch works with up to 150-Watt of dimmable LED/CFL or 600-Watt of incandescent/halogen, allowing you to control multiple bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, EcoSmart and Lighting Science. Use the rocker to adjust the light level for any activity or set the preset level to ensure lights always t

Long Description	Maestro LED+ Multiloc, Clamshell Ivory
------------------	--

Product Type	Maestro Led+ Multiloc Clam Ivory
--------------	----------------------------------

Special Features  
Controls dimmable 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Provides true dimming from each location (with companion dimmers). Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lutron
GTIN	00784276010511
Manufacturers Part Number	MACL-153MH-IV
UPC	784276010511

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Digital fade dimmer, multi-location/3-way/single-pole, clamshell packaging

## Packaging

Carton	1
Weight Per each	1.6

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
standard	UL, CSA, NOM