



MB2040PV200BTS Sloar MB-20/40 200A MB 225A Bus Non Euserc

Eaton Corp

| | |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | MB2040PV200BTS |
| Manufacturer | Eaton Corp |
| Description | Eaton Type BR Solar Power Center Meter Breaker, BR Solar-Ready, CSR Main Breaker, Over/Under Construction, 200A, 120/240V, 70 Max PV Input, 20 Spaces, 40 Circuits, 10 Kaic, Surface MTG, Nema 3R Galv. Steel Encl., Al 225A Bus, Oh/Ug Feed |
| Weight per unit | 39.8 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|-----------------|-------------------------------------|
| amperage rating | 200 A |
| dimensions | 34.7000 IN X 14.8000 IN X 6.0000 IN |
| Phase | 1 |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Also Known As... | Meter Socket Meter Box |
| Description | SLOAR MB-20/40 200A MB 225A BUS NON EUSERC |
| extra long description | ETN MB2040PV200BTS SOLAR MB-20/40, |
| Features | Eaton's Solar Power Centers feature industry-exclusive, factory-installed permanent markings, which help to ensure National Electrical Code (NEC) compliance and provide additional flexibility in PV sizing. The wide variety of configurations includes loadcenters and meters breakers, and becomes an all-in-one for both utility power and solar photovoltaic (PV) power. This all makes Eaton's Solar Power Centers not just the most complete line of Balance of System products, but also makes possible quick and ea |
| Long Description | Eaton Type BR Solar Power Center Meter Breaker, BR solar-ready, CSR main breaker, Over/under construction, 200A, 120/240V, 70 max PV input, 20 spaces, 40 circuits, 10 KAIC, Surface MTG, NEMA 3R Galv. Steel Encl., Al 225A bus, OH/UG feed |
| Product Type | Solar MB-20/40, 200A MB, 225A Bus |
| Special Features | Over/under construction |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786685690285 |
| Manufacturers Part Number | MB2040PV200BTS |
| UPC | 786685690285 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------------|
| Category Description | Meter Sockets |
| Type | Type BR solar power center meter breaker |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 39.75 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other |
| standard | UL Listed |