



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **MBE1224B125BTS MTR BRKR BR Euserc 125A MB 12/24 CKT BTM/Top Feed,** *Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | MBE1224B125BTS   |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Meter Breaker Euserc Type BR , BR2125 Main Breaker, 125A, 120/240V, Ring, 12 Spaces, 24 Circuits, 10 Kaic, Surface Mounting, Box Size A, Aluminum Bus, Overhead/Underground Feed, Four-Jaws, 1 Socket, #6-250 Kcmil Line, #14-2/0 Awg Ground |
| Weight per unit  | 40.0 (lbs/each)  |
| Product Category | Residential Meter Socket Circu   |

### Features

|                 |                                     |
|-----------------|-------------------------------------|
| amperage rating | 125 A                               |
| dimensions      | 5.3800 IN X 14.4400 IN X 23.8800 IN |
| Phase           | Single-phase                        |
| Voltage Rating  | 120/240 V                           |

### Descriptions

|                        |   |
|------------------------|---|
| Also Known As...       | Meter Box<br>Meter Socket   |
| Description            | MTR BRKR BR EUSERC 125A MB 12/24 CKT BTM/TOP FEED,  |
| extra long description | ETN MBE1224B125BTS Mtr brkr, BR, EUSE   |
| Features               | Eaton's Residential Meter Breakers save time and cost by providing contractors with all-in-one service entrance equipment. They allow for quick, flexible, simple installation, and can be used with BR- or CH-type branch circuit breaker styles. Constructed to be a self-contained durable enclosure and meet the latest NEC wire bending space requirements, they are particularly useful for residential metering in areas where utilities are deregulated, and the electrical contractor has to supply watt-hour meter so |
| Long Description       | Eaton Meter Breaker EUSERC Type BR , BR2125 main breaker, 125A, 120/240V, Ring, 12 spaces, 24 circuits, 10 kAIC, Surface mounting, Box size A, Aluminum bus, Overhead/underground feed, Four-jaws, 1 socket, #6-250 kcmil line, #14-2/0 AWG ground  |
| Product Type           | MTR BRKR, BR, Euserc, 125A MB, 12SP, BTM/Top,   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | EATON CUTLER-HAMMER |
| GTIN                      | 00782114890813      |
| Manufacturers Part Number | MBE1224B125BTS      |
| UPC                       | 782114890813        |

## Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Meter Sockets        |
| Type                 | Meter Breaker EUSERC |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 40 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs |
| standard    | UL Listed,EUSERC Approved  |