

Eaton MBEB200BTS

Catalog Number: MBEB200BTS

Eaton Meter Breaker EUSERC Type BR , CSR2200 main breaker, 200A, Single-phase, 120/240V, Ring, 10 kAIC, Surface mounting, Box size A, Aluminum bus, Overhead/underground feed, Four-jaws, 1 socket, #6-250 kcmil line, #6-250 kcmil ground



General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBEB200BTS
UPC	Product Length/Depth
782114849279	5.38 in
Product Height	Product Width
28.38 in	14.44 in
Product Weight	Warranty
37.75 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

AL : Alabama Power

AZ : Arizona Public Service Company

NM : El Paso Electric

TX : El Paso Electric

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Interrupt rating

10 kAIC

Box size

A

Enclosure

NEMA 3R

Ground

#6-250 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Resources

Brochures

[Eaton Emergency Disconnect Options at a Glance](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER WEST COAST STYLE](#)

Specifications and datasheets

[Eaton Specification Sheet - MBEB200BTS](#)

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

Single-phase

Used with

Type BR breakers

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)