



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MBX2040B150BTS Lever Bypass, 150A, 20/40 CKT Distribution, With B *Eaton Corp*

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | MBX2040B150BTS |
| Manufacturer | Eaton Corp |
| Description | Eaton Resi Meter Breaker, All-In-Ones, 150A, Aluminum, Nema 3R, Bottom and Top, #6-350 KCM22 Kaic, #6-350 KCMCSR, Surface Mounting, 40, Four-Jaw, 1, 20, Single-Phase, Ringless, Black Hills Energy, 120/240 Vac, Lever Bypass |
| Weight per unit | 40.0 (lbs/each) |
| Product Category | Main Circuit Breaker Modules |

Features

| | |
|---------------|-------------------------------------|
| dimensions | 4.9300 IN X 14.1900 IN X 39.8100 IN |
| Mounting Type | Surface |

Dimensions and Weight

| | |
|--------|-------|
| Height | 39.81 |
| Length | 4.93 |
| Width | 14.19 |

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | LEVER BYPASS, 150A, 20/40 CKT DISTRIBUTION, WITH B |
| extra long description | ETN MBX2040B150BTS LVR BYP, 150A, 2 |
| Features | Eaton's Residential Meter Breakers save time and cost by providing contractors with all-in-one service entrance equipment. They allow for quick, flexible, simple installation, and can be used with BR- or CH-type branch circuit breaker styles. Constructed to be a self-contained durable enclosure and meet the latest NEC wire bending space requirements, they are particularly useful for residential metering in areas where utilities are deregulated, and the electrical contractor has to supply watt-hour meter so |
| Long Description | Eaton resi meter breaker, All-in-ones, 150A, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm22 kAIC, #6-350 kcmCSR, Surface mounting, 40, Four-jaw, 1, 20, Single-phase, Ringless, Black Hills Energy, 120/240 Vac, Lever bypass |
| Product Type | LVR Byp, 150A, 20/40 CKT, With BWH Main |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786685460635 |
| Manufacturers Part Number | MBX2040B150BTS |
| UPC | 786685460635 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Meter Socket Accessories |
| Type | Residential meter breaker |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 40 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs |
| Mounting | Surface mounting |
| standard | UL Listed |