



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX34AA4D3F00 M-Max 3P 480V In/3P 480V Out 4.3A 2.0HP FS2 W Emc Eaton Corp

Catalog Number	MMX34AA4D3F00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Adjustable Frequency Ac Drives Basic Controller, Full Version, AA Software Design Series, Emc Filter, FS2 Frame, 380-480V, 460V, IP20 Enclosure Rating, 2 HP, 4.3A Output, 5.6A Input, Three-Phase In, Three-Phase Out
Weight per unit	3.0 (lbs/each)
Product Category	Ac Drives

Features

dimensions	3.5400 IN X 7.6800 IN X 4.0000 IN
Output Current	4.3 A

Descriptions

Description	M-MAX 3P 480V IN/3P 480V OUT 4.3A 2.0HP FS2 W EMC
extra long description	ETN MMX34AA4D3F0-0 MMX 480V,4.3A,2.
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series Adjustable Frequency AC Drives Basic Controller, Full version, AA software design series, EMC filter, FS2 frame, 380-480V, 460V, IP20 enclosure rating, 2 hp, 4.3A output, 5.6A input, Three-phase in, three-phase out
Product Type	MMX 480V, 4.3A, 2.0HP, FS2, W Emc
Special Features	Aa Software Design Series, Emc Filter

Manufacturer Information

Brand	Eaton
GTIN	00786685268811
Manufacturers Part Number	MMX34AA4D3F0-0
UPC	786685268811

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Packaging

Carton	1
Weight Per each	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

EN 60204-1,UL Listed,EN 61800-3,cUL Certified,EN
61800-5-1,C-Tick Compliant,EMC Category C2, C3, and C4 (Level
H): With an internal RFI filter option,RoHS Compliant,CE Marked