



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSCL0P153MIV Maestro 150W Led Occupancy Multi Ivory

Lutron

| | |
|------------------|---|
| Catalog Number | MSCL0P153MIV |
| Manufacturer | Lutron |
| Description | Maestro Occupancy Led+ Passive Infrared Occupancy/Vacancy Sensor That Automatically Controls The Lights In An Area In Ivory |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|----------------|---|
| body | Plastic |
| load | 600 W incandescent/halogen/140 W CFL/LED |
| media | Yes |
| sensing range | 900 ft2 (82 m2) major motion coverage/400 ft2 (36 m2) minor motion coverage |
| supply voltage | 120 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Ivory |
|-------|-------|

Descriptions

| | |
|------------------------|--|
| Description | MAESTRO 150W LED OCCUPANCY MULTI IVORY |
| extra long description | LUT MSCL-OP153M-IV MAESTRO LED+ PIR |
| Features | The Lutron Maestro LED+ Motion Sensor Dimmer Switch works just like a Lutron Maestro dimmer, with the addition of Lutron's advanced motion sensing technology to automatically and gradually turn the lights on and off. The LED+ Motion Sensor Dimmer Switch is rated for 150W dimmable LED or 600W Incandescent/Halogen bulbs. Install in a single pole, 3-way with existing switch, or with Maestro companion dimmers (MA-R/MSC-AD) to dim from up to 9 locations. Use the raise/lower buttons to adjust the brightness for |
| Long Description | Maestro occupancy LED+ passive infrared occupancy/vacancy sensor that automatically controls the lights in an area in ivory |
| Product Type | Maestro Led+ Pir Occ Sensor Box Ivory |
| Special Features | Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro LED+ fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft2 (81 m2)] major motion coverage and 20 ft x 20 ft (6 m x 6 m) [400 ft2 (36 m2)] minor motion coverage. Can be set to auto-on/auto-off or manual-on/auto-off. Adjustable timeout (1, 3, 5, 15, or 30 minutes) and h |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276054690 |
| Manufacturers Part Number | MSCL0P153MIV |
| UPC | 784276054690 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Occupancy sensor dimmer, multi-location/3-way/single-pole |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 0.4 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | 0 to 90% humidity, non-condensing. Indoor use only. |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, cUL, Title 20/24 certified |