



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MPP+7X7 3M Fire Barrier Moldable Putty Pads MPP+, 7 INX7 In *Minnesota Mining (3M)*

| | |
|------------------|---|
| Catalog Number | MPP+7X7 |
| Manufacturer | Minnesota Mining (3M) |
| Description | Moldable Putty Pad, Elastomer; Length 7 Inch; Width 6 Inch; Standard Package 20; 3M[T] Brand; Thickness 1/8 Inch; Includes A Handle |
| Weight per unit | 0.3300 (lbs/each) |
| Product Category | Tools - Paint, Chemicals, Etc. |

Features

| | |
|----------|-----------|
| Material | ELASTOMER |
|----------|-----------|

Dimensions and Weight

| | |
|--------|--------|
| Length | 7 INCH |
| Width | 7 INCH |

Descriptions

| | |
|------------------------|---|
| Additional Information | THICKNESS 1/8 INCH; INCLUDES A HANDLE |
| Commodity Description | Tools - Paint, Chemicals, Etc. |
| Description | 3M FIRE BARRIER MOLDABLE PUTTY PADS MPP+, 7 INX7 IN |
| Long Description | MOLDABLE PUTTY PAD, ELASTOMER; LENGTH 7 INCH; WIDTH 6 INCH; STANDARD PACKAGE 20; 3M[T] BRAND; THICKNESS 1/8 INCH; INCLUDES A HANDLE |
| Product Type | Moldable Putty Pad |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Minnesota Mining (3M) |
| GTIN | 00051115165092 |
| Manufacturers Part Number | MPP+7INX7 |
| Model | MPP+ |
| UPC | 051115165092 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------|
| Category Description | Jackets, Boots, Shirts, Workwear |
|----------------------|----------------------------------|

Packaging

| | |
|------------------|-------------|
| Carton | 20 |
| Standard Package | 20 PER CASE |
| Weight Per each | 0.33 |

Uses, Certifications, and Standards

| | |
|----------|-------------|
| Approval | UL, CUL, FM |
|----------|-------------|

Pillows and Putty

3M™ Fire Barrier Self-Locking Pillows



Self-contained, highly intumescent pillows are designed to firestop a wide variety of through-penetrations including cable trays, conduit and blank openings. Interlocking strips hold pillows securely together yet release easily for retrofit or reuse—just remove and replace pillows as needed.

- No wire mesh reduces safety issues
- Easy to install, easy to remove and reuse
- No cutting and no mess—just lock pillows together, compress and place (use 3M™ Fire Barrier Moldable Putty+ around edges to ensure proper seal)
- No graphite
- Excellent aging properties
- Available in 2" x 4" x 9" (small), 2" x 6" x 9" (medium) and 3" x 6" x 9" (large) pillow sizes
- Provides up to 3-hour UL Listed systems (in up to a 540 square inch opening)

3M™ Fire Barrier Pillows




Stackable and conformable firestop pillows for new and retrofit projects.

- No wire mesh or graphite
- Excellent aging properties

- Available in 2" x 4" x 9" (small), 2" x 6" x 9" (medium) and 3" x 6" x 9" (large) pillow sizes
- Provides up to 3-hour UL Listed systems (in up to a 540 square inch opening)

3M™ Fire Barrier Moldable Putty+



3M Fire Barrier Moldable Putty+ is designed for use as a one-part, 100% solids intumescent firestop that restores the integrity of fire-rated building construction.

- Ideal for construction gaps, cable, insulated pipe, electrical conduit and metal pipe
- Designed to provide up to a 4-hour fire rating
- UL-classified for telecommunications applications (interduct, fiber optic and cables)
- Remains pliable and flexible
- Won't dry out or crumble
- Convenient pad and stix form
- Non-halogen formula
- Reenterable
- Adheres to all common building surfaces including metal and plastic electrical boxes
- Available in both 4S and 5S electrical box sizes
- Provides draft and cold smoke seal even before temperature increases
- Intumescent and expands to form a hard char that prevents the transmission of hot gases and fire
- Great for building maintenance applications

Specifications and Ordering Information for 3M™ Fire Barrier Pillows and Putty

| Product | UPC (051115-) | Size | Volume | Case Qty. |
|--|---------------|---|-----------------------|-----------|
| FIRE BARRIER PILLOWS | | | | |
| FB 249 Pillow | 16508-5 | 1/8" x 4" x 8" (3,2 x 102 x 203 mm) | N/A | 24 |
| FB 269 Pillow | 16531-3 | 2" x 6" x 9" | N/A | 16 |
| FB 369 Pillow | 16532-0 | 3" x 6" x 9" | N/A | 20 |
| FIRE BARRIER SELF-LOCKING PILLOWS | | | | |
| SLP-Small | 16578-3 | 2" x 4" x 9" | N/A | 24 |
| SLP-Medium | 16579-0 | 2" x 6" x 9" | N/A | 16 |
| SLP-Large | 16580-6 | 3" x 6" x 9" | N/A | 20 |
| MOLDABLE PUTTY PADS AND STIX | | | | |
| MPP+ 4" x 8" | 16508-5 | 1/8" x 4" x 8" (3,2 x 102 x 203 mm) | 4 in. ³ | 100 each |
| MPP+ 7" x 7" | 16509-2 | 1/8" x 7" x 7" (3,2 x 178 x 178 mm) | 6.12 in. ³ | 20 each |
| MPP+ 9.5" x 9.5" | 16510-8 | 1/8" x 9.5" x 9.5" (3,2 x 241,3 x 241,3 mm) | 11.3 in. ³ | 20 each |
| MP+ Stix | 16526-9 | 1.5" x 11" (40,6 x 279 mm) | 21.2 in. ³ | 10 each |
| MP+ Stick | 16561-0 | 1.4" x 6" (183 mm) | N/A | 12 each |

Put heat
in its
place

