



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSB202WH Maestro DV 6A Occupancy 3WAY Ditec White

Lutron

Catalog Number	MSB202WH
Manufacturer	Lutron
Description	Maestro Dual Technology (Dual Tech), Partial-On Occupancy Sensor Switch, Applies Exclusive XCT Technology For Minor and Fine Motion Detection. Meets Title 24 Requirements For Multi-Level Lighting In White
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
indicator	Smart ambient light detection (ALD)/Fixed ambient light detection
load	6 A@10-277 VAC lights/4.4 A (0.167 HP)@120 VAC fan
media	Yes
sensing range	900 ft ² (82 m ²) major motion coverage/400 ft ² (36 m ²) minor motion coverage
supply voltage	120 to 277

Material, Color, and Finish

Color	White
Finish	Gloss



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MAESTRO DV 6A OCCUPANCY 3WAY DLTEC WHITE
extra long description	LUT MS-B202-WH MAESTRO 2-CIR DT OCC
Features	The Lutron Maestro Dual Circuit Dual-Tech Motion Sensor Switch combines two switches with ultrasonic waves and passive infrared (PIR) technology to ensure reliable automatic sensing. Each circuit can be controlled independently as an occupancy/partial-on sensor to meet energy codes (e.g., ASHRAE). This Dual Circuit Dual-Tech motion sensor controls 2 individual single pole circuits each rated for up to 6A of lighting or 4.4A (1/6HP) fan motors. The sensor has a 180-degree field of view (900 sq ft major moti
Long Description	Maestro Dual Technology (Dual Tech), partial-on occupancy sensor switch, applies exclusive XCT Technology for minor and fine motion detection. Meets Title 24 requirements for multi-level lighting in white
Product Type	Maestro 2-Cir DT Occ Sens In White
Special Features	Applies Lutron's exclusive XCT Technology (Dual Tech) to the ultrasonic as well as the passive infrared technology in this sensor to create a product that can detect very fine motion, such as typing. Includes all of the great features found in the rest of the Maestro sensor family, including: adaptive relay switching, smart ambient light detection, and simple button presses for changing settings. XCT technology for major, minor, fine, and very fine motion detection. 180 degree field-of-view. Tamper-resista

Manufacturer Information

Brand	Lutron
GTIN	00784276086288
Manufacturers Part Number	MS-B202-WH
UPC	784276086288

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy sensor switch, dual-circuit, multi-location/3-way/single-pole

Packaging

Carton	1
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, NOM