




## TWO GANG MULTI-CONFIGURATION FLIP COVERS

Two Gang Universal Metal Flip Covers  
25-in-1

D15



Catalog #: MX2050Z

## APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.  
N/A

## PRODUCT FEATURES

Heavy duty die-cast metal construction  
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.  
Pre-configured for GFCI with patented knockout technology for alternate devices  
Includes attached gasket and mounting hardware  
Premium powder coat finish  
Lockable tab

## UL LISTED

File E212332

## NEMA

3R Rated

## NEC

2014 Compliant (article 406.9A)

## US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

## GENERAL PRODUCT INFORMATION

Color: Bronze

## CONFIGURATION

Gangs: 2

## PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

## PACKAGING


Package Type: Shrink  
Std. Pkg.: 4  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 48.50  
Ship Carton Length (in.): 5.12  
Ship Carton Width (in.): 5.31  
Ship Carton Height (in.): 6.50  
Ctn Weight (Lbs.): 1.94  
Pallet Qty: 960.00  
UPC Number: 092326112802  
I2of5: 30092326112803



## TWO GANG MULTI-CONFIGURATION FLIP COVERS

Two Gang Universal Metal Flip Covers  
25-in-1

D15



Catalog #: MX2050Z

## APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.  
N/A

## PRODUCT FEATURES

Heavy duty die-cast metal construction  
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.  
Pre-configured for GFCI with patented knockout technology for alternate devices  
Includes attached gasket and mounting hardware  
Premium powder coat finish  
Lockable tab

## UL LISTED

File E212332

## NEMA

3R Rated

## NEC

2014 Compliant (article 406.9A)

## US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

## GENERAL PRODUCT INFORMATION

Color: Bronze

## CONFIGURATION

Gangs: 2

## PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

## PACKAGING

Package Type: Shrink  
Std. Pkg.: 4  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 48.50  
Ship Carton Length (in.): 5.12  
Ship Carton Width (in.): 5.31  
Ship Carton Height (in.): 6.50  
Ctn Weight (Lbs.): 1.94  
Pallet Qty: 960.00  
UPC Number: 092326112802  
I2of5: 30092326112803