


## RaynGuard<sup>®</sup> 1-Gang Weatherproof In-Use Cover

Catalog #:  
MX3200



MX3200



### FEATURE BENEFIT

Extra Deep, provides 3-1/2 inches of depth inside while in use



### PRODUCT FEATURES

- Heavy duty die-cast aluminum construction
- Patented QuickFit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab (fits up to 1/8 in. shackable)
- Premium Powder Coat

### APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use

### CERTIFICATIONS



NEMA 3R Rated  
NEC - Extra Duty Rated

### PRODUCT SPECIFICATIONS

UPC Number:	092326104760
Ea Length/Depth (in.):	3.54
Ea Width (in.):	3.37
Ea Height (in.):	6.12
Wt. Ea. (Lbs.):	0.620
Color:	Gray
Gangs:	1
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

### SHIPPING

I2of5:	40092326104768
Standard Carton Qty:	4
Min Order Qty:	1
Ship Carton Length (in.):	14.61
Ship Carton Width (in.):	3.86
Ship Carton Height (in.):	7.08
Ship Carton Weight (Lbs.):	2.80
Pallet Qty:	720



**COMMERCIAL  
CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

TayMac  
2520 E. University Dr.  
Tempe, AZ 85281  
800-526-5416  
[www.hubbell.com/taymac/en](http://www.hubbell.com/taymac/en)

Revision 1, July 2018




## RaynGuard<sup>®</sup> 1-Gang Weatherproof In-Use Cover

Catalog #:  
MX3200



MX3200



### FEATURE BENEFIT

Extra Deep, provides 3-1/2 inches of depth inside while in use



### PRODUCT FEATURES

- Heavy duty die-cast aluminum construction
- Patented QuickFit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab (fits up to 1/8 in. shackable)
- Premium Powder Coat

### APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use

### CERTIFICATIONS



NEMA 3R Rated  
NEC - Extra Duty Rated

### PRODUCT SPECIFICATIONS

UPC Number:	092326104760
Ea Length/Depth (in.):	3.54
Ea Width (in.):	3.37
Ea Height (in.):	6.12
Wt. Ea. (Lbs.):	0.620
Color:	Gray
Gangs:	1
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

### SHIPPING

I2of5:	40092326104768
Standard Carton Qty:	4
Min Order Qty:	1
Ship Carton Length (in.):	14.61
Ship Carton Width (in.):	3.86
Ship Carton Height (in.):	7.08
Ship Carton Weight (Lbs.):	2.80
Pallet Qty:	720



**COMMERCIAL  
CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

TayMac  
2520 E. University Dr.  
Tempe, AZ 85281  
800-526-5416  
[www.hubbell.com/taymac/en](http://www.hubbell.com/taymac/en)



Revision 1, July 2018