

NCVT-5 NON-CONTACT VOLTAGE TESTER

With Laser Pointer



70 – 1000V AC

DUAL-RANGE

12 – 1000V AC



**CAT IV
1000V**



NON-CONTACT VOLTAGE TESTER WITH LASER POINTER

The Klein Tools NCVT-5 is a dual-range non-contact voltage tester (NCVT) with a laser pointer. It can be set to detect voltage from 70 to 1000V AC (in Mode 1) or from 12-1000V AC (in Mode 2). The laser pointer can function independent of, or simultaneously with the NCVT.

70 – 1000V AC

DUAL-RANGE

12 – 1000V AC



**CAT IV
1000V**

NCVT-5 can detect voltage in two distinct modes*:

Mode 1: 70 to 1000V AC


Mode 2: 12 to 1000V AC

*defined by the voltage ranges to which the tester is sensitive

- Power On/Mode LEDs
- Voltage Detection LEDs (inside tip)
- Auto Power Off (APO) conserves and extends battery life
- Lightweight, compact tester with pocket clip for easy storage and quick access.



Patent #D750985



**2x AAA
INCLUDED**



THE POWER-ON INDICATOR LEDs WILL INDICATE THE CURRENTLY ACTIVE MODE.
DETECTS AC VOLTAGE WITH AUDIBLE & VISUAL INDICATORS

Cat. No.	UPC 0-92644+	Description	Overall Length
NCVT-5	69143-0	Non-Contact Voltage Tester w/ Laser Pointer	6" (152 mm)
NCVT-4IR	69061-7	Non-Contact Voltage Tester w/ Infrared Thermometer	6.25" (159 mm)
NCVT-3	69008-2	Non-Contact Voltage Tester w/ Flashlight	6" (152 mm)
NCVT-2	69002-0	Non-Contact Voltage Tester (Dual Range)	5.5" (140 mm)
NCVT-1	69000-6	Non-Contact Voltage Tester	5.5" (140 mm)

See our complete line of **Test & Measurement Products**

www.kleintools.com



© 2018 Klein Tools, Inc.
Lincolnshire, IL 60069
94819 Rev. 07/18 A



NCVT-5 NON-CONTACT VOLTAGE TESTER

With Laser Pointer



70 – 1000V AC

DUAL-RANGE

12 – 1000V AC



3 m

**CAT IV
1000V**

**KLEIN
TOOLS**



NON-CONTACT VOLTAGE TESTER WITH LASER POINTER

The Klein Tools NCVT-5 is a dual-range non-contact voltage tester (NCVT) with a laser pointer. It can be set to detect voltage from 70 to 1000V AC (in Mode 1) or from 12-1000V AC (in Mode 2). The laser pointer can function independent of, or simultaneously with the NCVT.

70 – 1000V AC

DUAL-RANGE

12 – 1000V AC



**CAT IV
1000V**

NCVT-5 can detect voltage in two distinct modes*:

Mode 1: 70 to 1000V AC


Mode 2: 12 to 1000V AC

*defined by the voltage ranges to which the tester is sensitive

- Power On/Mode LEDs
- Voltage Detection LEDs (inside tip)
- Auto Power Off (APO) conserves and extends battery life
- Lightweight, compact tester with pocket clip for easy storage and quick access.



Patent #D750985



**2x AAA
INCLUDED**



THE POWER-ON INDICATOR LEDs WILL INDICATE THE CURRENTLY ACTIVE MODE.
DETECTS AC VOLTAGE WITH AUDIBLE & VISUAL INDICATORS

Cat. No.	UPC 0-92644+	Description	Overall Length
NCVT-5	69143-0	Non-Contact Voltage Tester w/ Laser Pointer	6" (152 mm)
NCVT-4IR	69061-7	Non-Contact Voltage Tester w/ Infrared Thermometer	6.25" (159 mm)
NCVT-3	69008-2	Non-Contact Voltage Tester w/ Flashlight	6" (152 mm)
NCVT-2	69002-0	Non-Contact Voltage Tester (Dual Range)	5.5" (140 mm)
NCVT-1	69000-6	Non-Contact Voltage Tester	5.5" (140 mm)

See our complete line of **Test & Measurement Products**

www.kleintools.com



© 2018 Klein Tools, Inc.
Lincolnshire, IL 60069
94819 Rev. 07/18 A

