



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NFFLDSC15TUNV 51W Led Flood Trunion 40K

Cooper Lighting Solutions

Catalog Number	NFFLDSC15TUNV
Manufacturer	Cooper Lighting Solutions
Description	Flood Light, Die-Cast Aluminum, 120 to 277 V Ac;347 V Ac;480 V Ac, 51 W, 70, 5797 LM Brightness (Lumens), 0.45 A @ 120 V;0.25 A @ 208 V;0.22 A @ 240 V;0.19 A @ 277 V;0.16 A @ 347 V;0.13 A @ 480 V, 4000 K, Led Lamp, Polyester Powder Coat, Copper, 8-7/32 In Length, 7-1/2 In Width, 10-15/16 In Height, Tempered Glass Lens Material, Trunion Mount, +40 °C Operating Temperature, -40 °C Operating Temperature, 50000 H Average Life, 5 Yr Warranty, 13 LB
Weight per unit	13.3 (lbs/each)
Product Category	Led Floodlights

Features

amperage rating	0.184 at 277V
Ballast Type	N/A
battery	N/A
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	5,797
Number of Lamps	1
Shape	Rectangular

Dimensions and Weight

Size	12.784 IN Length 10.909 IN Width 11.068 IN Height
------	---

Descriptions

Description	51W LED FLOOD TRUNION 40K
extra long description	CLS NFFLD-S-C15-T-UNV F SMALL, 500
Special Features	Die-cast aluminum housing, driver compartment and driver door

Manufacturer Information

Brand	LUMARK
GTIN	00080083760275
UPC	080083760275

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	13.3399

Uses, Certifications, and Standards

Mounting	TRUNNION
standard	UL/cUL Listed - Wet Location;RoHS Compliant