

Primary Main or Run Line Side	Secondary Tap Load Side	Part Number 100kA SCCR	Number of Wire Ports by Wire Range	Block Size	Maximum Amp per Pole	Part Number 10kA SCCR	BURNDY Part Number 100kA SCCR	ILSCO Part Number 100kA SCCR	MARATHON Part Number 100kA SCCR	COOPER BUSSMAN Part Number 100kA SCCR
-	-	CSNPDB	REPLACEMENT COVER FOR SMALL BLOCK	SMALL	-	CS	BDBSHCCOVER	-	-	-
-	-	CMNPDB	REPLACEMENT COVER FOR MEDIUM BLOCK	MEDIUM	-	CM	BDBMHCCOVER	-	-	-
-	-	CLNPDB	REPLACEMENT COVER FOR LARGE BLOCK	LARGE	-	CL	BDBLHCCOVER	-	-	-
		NPDB-11-2/0-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 2/0-14, LOAD 1 X 2/0-14	SMALL	175	AS-K1-K1 NOT FINGER SAFE	BDBSCS1P1 NOT FINGER SAFE BDBSCS1P1FS FINGER SAFE	PDH-11-2/0-1 NOT FINGER SAFE	-	PDBFS204 FINGER SAFE
		NPDB-11-350-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 350-6, LOAD 1 X 350-6	MEDIUM	310	AM-P1-P1 NOT FINGER SAFE	BDBMCS3U1 NOT FINGER SAFE BDBMCS3U1FS FINGER SAFE	-	-	PDBFS303 FINGER SAFE
		NPDB-11-500-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 500-4, LOAD 1 X 500-4	MEDIUM	380	AM-R1-R1 NOT FINGER SAFE	BDBLCS5W1 NOT FINGER SAFE BDBLCS5W1FS FINGER SAFE	-	-	-
		NPDB-11-600-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 600-4, LOAD 1 X 600-4	MEDIUM	420	-	-	PDH-11-600-1 NOT FINGER SAFE	-	-
		NPDB-11-750-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 750-250, LOAD 1 X 750-250	LARGE	475	-	-	-	-	-
		NPDB-14-2/0-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 2/0-14, LOAD 4 X 4-14	SMALL	175	AS-K1-H4 NOT FINGER SAFE	BDBSCS1C1 NOT FINGER SAFE BDBSCS1C1FS FINGER SAFE	PDH-14-2/0-1 NOT FINGER SAFE	FPB23570CH FINGER SAFE	PDBFS220 FINGER SAFE
		NPDB-14-500-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 500-4, LOAD 4 X 4/0-14	LARGE	380	AL-R1-M4 NOT FINGER SAFE	BDBMCS5M1 NOT FINGER SAFE BDBMCS5M1FS FINGER SAFE	-	-	-
		NPDB-14-750-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 750-250, LOAD 4 X 250-6	LARGE	475	-	-	-	-	-
		NPDB-16-350-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 350-6, LOAD 6 X 2/0-14	LARGE	375	AL-P1-K6 NOT FINGER SAFE	BDBLCS3K1 NOT FINGER SAFE BDBLCS3K1FS FINGER SAFE	-	-	-
		NPDB-16-500-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 500-4, LOAD 6 X 2/0-14	LARGE	380	AL-R1-K6 NOT FINGER SAFE	BDBLCS5K1 NOT FINGER SAFE BDBLCS5K1FS FINGER SAFE	-	-	PDBFS330 FINGER SAFE
		NPDB-16-600-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 600-4, LOAD 6 X 2/0-14	LARGE	420	-	-	-	-	-
		NPDB-112-500-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 500-4, LOAD 12 X 4-14	LARGE	380	AM-R1-H12 NOT FINGER SAFE	-	-	-	-
		NPDB-112A-350-1 FINGER SAFE	PDB, 1 POLE, LINE 1 X 350-6, LOAD 12 X 4-14	MEDIUM	310	AM-P1-H12 NOT FINGER SAFE	BDBLCS3A1 NOT FINGER SAFE BDBLCS3A1FS FINGER SAFE	-	-	PDB370-1 FINGER SAFE

Primary Main or Run Line Side	Secondary Tap Load Side	Part Number 100kA SCCR	Number of Wire Ports by Wire Range	Block Size	Maximum Amp per Pole	Part Number 10kA SCCR	BURNDY Part Number 100kA SCCR	ILSCO Part Number 100kA SCCR	MARATHON Part Number 100kA SCCR	COOPER BUSSMAN Part Number 100kA SCCR
		NPDB-22-2/0-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 2/0-14, LOAD 2 X 2/0-14	MEDIUM	350	AS-K2-K2 NOT FINGER SAFE	BDBLCS6A1 NOT FINGER SAFE BDBLCS6A1FS FINGER SAFE	-	-	-
		NPDB-22-350-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 350-6, LOAD 2 X 350-6	LARGE	620	AL-P2-P2 NOT FINGER SAFE	BDBLCS4T1 NOT FINGER SAFE BDBLCS4T1FS FINGER SAFE	PDH-22-350-1 NOT FINGER SAFE	-	PDBFS500 FINGER SAFE
		NPDB-22-500-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 500-4, LOAD 2 X 500-4	LARGE	760	AL-R2-R2 NOT FINGER SAFE	BDBLCS6V1 NOT FINGER SAFE BDBLCS6V1FS FINGER SAFE	PDH-22-500-1 NOT FINGER SAFE	-	PDBFS504 FINGER SAFE
		NPDB-22-600-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 600-4, LOAD 2 X 600-4	LARGE	840	-	-	-	-	-
		NPDB-24-500-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 500-4, LOAD 4 X 4/0-6	LARGE	760	AL-R2-M4 NOT FINGER SAFE	BDBLCS6R1 NOT FINGER SAFE BDBLCS6R1FS FINGER SAFE	-	-	-
		NPDB-24-600-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 600-4, LOAD 4 X 4/0-6	LARGE	840	-	-	-	-	-
		NPDB-26-2/0-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 2/0-14, LOAD 6 X 4-14	MEDIUM	350	AM-K2-I6 NOT FINGER SAFE	BDBMCS2F1 NOT FINGER SAFE BDBMCS2F1FS FINGER SAFE	PDH-26-2/0-1 NOT FINGER SAFE	-	-
		NPDB-26-350-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 350-6, LOAD 6 X 2/0-14	LARGE	620	AL-P2-K6 NOT FINGER SAFE	BDBLCS4K1 NOT FINGER SAFE BDBLCS4K1FS FINGER SAFE	-	-	-
		NPDB-26-500-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 500-4, LOAD 6 X 2/0-14	LARGE	760	AL-R2-K6 NOT FINGER SAFE	BDBLCS6K1 NOT FINGER SAFE BDBLCS6K1FS FINGER SAFE	-	-	-
		NPDB-26-600-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 600-4, LOAD 6 X 2/0-14	LARGE	840	-	-	-	-	-
		NPDB-212-350-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 350-6, LOAD 12 X 4-14	LARGE	620	AL-P2-H12 NOT FINGER SAFE	-	-	-	PDBFS377 FINGER SAFE
		NPDB-212-500-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 500-4, LOAD 12 X 4-14	LARGE	760	AL-R2-H12 NOT FINGER SAFE	BDBLCS6A1 NOT FINGER SAFE BDBLCS6A1FS FINGER SAFE	PDH-14-2/0-1 NOT FINGER SAFE	-	-
		NPDB-212-600-1 FINGER SAFE	PDB, 1 POLE, LINE 2 X 600-4, LOAD 12 X 4-14	LARGE	840	-	-	-	-	-

*FOR TECHNICAL ASSISTANCE WITH POWER DISTRIBUTION BLOCKS
CALL 1-800-321-5847 AND ASK FOR TECHNICAL ASSISTANCE

SEE REVERSE FOR MORE →