



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NRG356L4KUPC Wallpack Led 1513 LM 4K 1

Hubbell Lighting, Inc.

Catalog Number	NRG356L4KUPC
Manufacturer	Hubbell Lighting, Inc.
Description	NRG Perimeter, Wallpack, Wall (Surface), Led, Number Of Leds: 56, 4000 K, 80 Cri, Lamp Included: Yes, Polycarbonate, Button Photocontrol, 100 Ma, 16.6 W, 120-277 Vac, Dark Bronze Matte Textured.
Weight per unit	5.4 (lbs/each)
Product Category	Lighting

Features

Lamp Included	Yes
Lamp Type	LED
Material	Aluminum
Voltage Rating	120-277
Wattage	16.6

Material, Color, and Finish

Color	Dark Bronze Matte Textured
-------	----------------------------

Descriptions

Description	WALLPACK LED 1513 LM 4K 1
extra long description	HUB-LT NRG-356L-4K-U-PC NRG®, LED,
Long Description	NRG Perimeter, Wallpack, Wall (surface), LED, Number of LEDs: 56, 4000 K, 80 CRI, Lamp Included: Yes, Polycarbonate, Button Photocontrol, 100 mA, 16.6 W, 120-277 VAC, Dark Bronze Matte Textured.
Product Type	NRG®, Led, Number Of Leds 56, 4000 K

Manufacturer Information

Brand	Exo Outdoor Lighting
GTIN	00785988031405
Manufacturers Part Number	NRG-356L-4K-U-PC
UPC	785988031405

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wallpack

Packaging

Carton	1
Weight Per each	5.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Manufacturing;Warehouse;Offices;Hospitality;Retail;Automotive Dealers;Educational;Healthcare
Frequency Rating	50/60
Mounting	Wall (surface)
standard	UL;CSA