



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NTC150 1-1/2" Rigid Threadless Raintight Connector

Appleton/Oz Gedney

Catalog Number	NTC150
Manufacturer	Appleton/Oz Gedney
Description	Compression Connector, Size: 1-1/2 In, Connection: Male Threaded X Compression, Material: Malleable Iron, Length: 2.01 In, Thread Length: 0.63 In, Diameter: 2.69 In, Standard: UI 514B, UI File Number E14814, Nema FB-1, For Use to Secure and Terminate Steel Emt to Knockouts and Concrete Tight Box
Weight per unit	0.6800 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded X Compression
Material	Malleable Iron

Dimensions and Weight

Size	1-1/2
------	-------

Descriptions

Description	1-1/2" RIGID THREADLESS RAIN TIGHT CONNECTOR
extra long description	APP NTC-150 1-1/2 IN CONN NO THRD R
Long Description	Compression Connector, Size: 1-1/2 IN, Connection: Male Threaded X Compression, Material: Malleable Iron, Length: 2.01 IN, Thread Length: 0.63 IN, Diameter: 2.69 IN, Standard: UL 514B, UL File Number E14814, NEMA FB-1, For Use To Secure And Terminate Steel EMT To Knockouts And Concrete Tight Box
Product Type	1-1/2 In Conn No THRD RGD Cond
Special Features	Concretetight

Manufacturer Information

Brand	Appleton
GTIN	00781381637909
Manufacturers Part Number	NTC-150
UPC	781381637909

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression Connector

Packaging

Carton	2
Package	10
Weight Per each	0.68



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Use To Secure And Terminate Steel EMT To Knockouts And
Concrete Tight Box

standard

UL 514B, UL File Number E14814, NEMA FB-1