

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P2006-09

Bravo

Three-light bath finished in Brushed Nickel with etched glass shades scaled across a slightly arching, pointed arm. Generously balanced glass shades add distinction and provide pleasing illumination to your room. Coordinating fixtures from this collection let you decorate an entire home with confidence and style.

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched glass shades

Width: 26-3/4"

Height: 8-3/4"

Depth: 8-3/4"

H/CTR: 6"

Glass: 7-1/4" dia.

Height: 5-3/8"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|--|---|
| <p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Mounts in "up" or "down" position</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>9" W., 5", 1"</p> | <p>Threaded socket ring secures glass</p> <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p> | <p>Quantity: 3</p> <p>100W Medium Base</p> <p>Medium ceramic sockets</p> | <p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available</p> |

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P2006-09

Bravo

Three-light bath finished in Brushed Nickel with etched glass shades scaled across a slightly arching, pointed arm. Generously balanced glass shades add distinction and provide pleasing illumination to your room. Coordinating fixtures from this collection let you decorate an entire home with confidence and style.

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched glass shades

Width: 26-3/4"

Height: 8-3/4"

Depth: 8-3/4"

H/CTR: 6"

Glass: 7-1/4" dia.

Height: 5-3/8"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|--|---|
| <p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Mounts in "up" or "down" position</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>9" W., 5", 1"</p> | <p>Threaded socket ring secures glass</p> <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p> | <p>Quantity: 3</p> <p>100W Medium Base</p> <p>Medium ceramic sockets</p> | <p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available</p> |