

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P2708-09

Gather

Gather possesses a smart simplicity to complement today's home. This three-light bath bracket contains etched glass shades which add distinction and provide pleasing illumination to your room. Featuring a glamorous Brushed Nickel finished frame, this collection allows you to decorate an entire home with confidence and style.

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched glass shades

Width: 24"

Height: 7-1/2"

Depth: 6-1/2"

H/CTR: 2-1/2"

Glass: 4" dia.

Height: 4-13/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Wall mounted</p> <p>Mounting strap for outlet box included</p> <p>Mounts in "up" or "down" position</p> <p>Back plate covers a standard 4" hexagonal recessed outlet box</p> <p>24" W., 4-9/16"</p>	<p>Threaded socket ring secures glass</p> <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 3</p> <p>100W Medium Base</p> <p>Medium ceramic sockets</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available</p>

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Incandescent

P2708-09

Gather

Gather possesses a smart simplicity to complement today's home. This three-light bath bracket contains etched glass shades which add distinction and provide pleasing illumination to your room. Featuring a glamorous Brushed Nickel finished frame, this collection allows you to decorate an entire home with confidence and style.

Width: 24"
Height: 7-1/2"
Depth: 6-1/2"
H/CTR: 2-1/2"

Category: Bath & Vanity

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched glass shades

Glass: 4" dia.
 Height: 4-13/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Mounts in "up" or "down" position Back plate covers a standard 4" hexagonal recessed outlet box 24" W., 4-9/16"	Threaded socket ring secures glass Pre-wired 6" of wire supplied 120V	Quantity: 3 100W Medium Base Medium ceramic sockets	UL-CUL Damp location listed 1 year warranty Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available