



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **P8222830K 7.25" Led 1LT RND FLSH MN Triac Dimming - No HRDWR** *Progress Lighting*

Catalog Number	P8222830K
Manufacturer	Progress Lighting
Description	The P8222 Delivers A Solution For Flush Mount, For Both Residential and Commercial Markets. In Addition, The P8222 Is Wet Located, Title 24 - JA8 - 2019 and Is A Cost Effective Solution For Fire Rated Applicaiton. The P8222 Luminaire Unites Performance, Cost and Safety Benefits.
Weight per unit	1.2 (lbs/each)
Product Category	Led Surface Architectural & SP

### **Features**

amperage rating	0.122
indoor/outdoor	Indoor
Lamp Included	Yes
Lamp Type	LED
Light Source	LED
Material	Die-Cast Aluminum
Number of Lamps	1
pallet quantity	480
Power Source	Hardwired
Spacing	1.2
Voltage Rating	120
Wattage	13.6

### **Material, Color, and Finish**

Color	White
Finish	Painted
Style	Modern;Transitional

### **Dimensions and Weight**

Height	1.1875
Length	7.25
Width	7.25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	7.25" LED 1LT RND FLSH MN TRIAC DIMMING - NO HRDWR
extra long description	PROG P8222-28-30K P8222-28-30K 7.25
Long Description	The P8222 delivers a solution for flush mount, for both residential and commercial markets. In addition, the P8222 is wet located, Title 24 - JA8 - 2019 and is a cost effective solution for fire rated applicaiton. The P8222 luminaire unites performance, cost and safety benefits.
Product Type	P8222-28-30K 7.25IN Led Flush MT T24

## Manufacturer Information

Brand	Progress Lighting
GTIN	00785247205615
Manufacturers Part Number	P8222-28-30K
UPC	785247205615

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Flush-Mount

## Packaging

Carton	1
Weight Per each	1.16

## Uses, Certifications, and Standards

Frequency Rating	60
standard	FCC Title 47, Part 15, Class B