



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P83I Smooth Wallplate 3G Duplex Iv

Pass & Seymour/Legrand

| | |
|------------------|----------------------------------|
| Catalog Number | P83I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Wall Plate, 3-Gang Duplex |
| Weight per unit | 0.1300 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|-------------------|
| cutout | Receptacle |
| indoor/outdoor | Indoor |
| insulation | Bare |
| media | Yes |
| Mounting Type | Strap Mounted |
| Number of Gangs | 3 |
| orientation | Vertical |
| Wall Plate Type | Duplex Receptacle |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Construction | Plastic |
| Description | SMOOTH WALLPLATE 3G DUPLEX IV |
| extra long description | P&S SP83I SMOOTH WP 3G DUPLEX IV |
| Long Description | Smooth Wall Plate, 3-Gang Duplex |
| Product Type | Smooth WP 3G Duplex Iv |
| Special Features | Non-combustible mar-proof material, seven standards colors, individually wrapped |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007187649 |
| Manufacturers Part Number | SP83I |
| UPC | 785007187649 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 15 |
| Weight Per each | 0.13 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |