



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PD5NEWH Caseta 500W Elv Mult W/Neutral White *Lutron*

Catalog Number	PD5NEWH
Manufacturer	Lutron
Description	Lutron Caseta Wireless Elv+ Smart Dimmer Switch, With Phase Selectable Dimming For Led (250W), MLV (400W), Elv (500W), and Incandescent/Halogen (500W) Lighting, 120V, White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Push button
Voltage Rating	120
Wattage	500

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	CASETA 500W ELV MULT W/NEUTRAL WHITE
extra long description	LUT PD-5NE-WH Cas ta ELV Dimmer 250
Features	The Caseta ELV+ Smart Dimmer Switch with phase selectable dimming works with up to 250W of dimmable LED, 500W of incandescent/halogen/electronic low-voltage (ELV), or 400-Watt of magnetic low-voltage (MLV); Neutral wire connection and 10-Watt minimum load required for all load types. Out of the box, the dimmer is set to reverse phase for ELV/incandescent/halogen light loads. However, since it is phase selective, the dimmer output can be changed to forward phase for MLV lighting loads and other certain LED
Long Description	Lutron Caseta Wireless ELV+ Smart Dimmer Switch, with Phase Selectable Dimming for LED (250W), MLV (400W), ELV (500W), and Incandescent/Halogen (500W) lighting, 120V, White
Product Type	Cas Ta Elv Dimmer 250W Led White
Special Features	Controls 250 W LED (screw-base), 500 W incandescent/halogen, 400 VA (300 W) magnetic low-voltage, 500 W electronic low-voltage, 400 W Hi-lume 1 percent 2-wire LED driver, or 3.3 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes.

Manufacturer Information

Brand	Lutron
GTIN	00784276217699
Manufacturers Part Number	PD-5NE-WH
UPC	784276217699

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall dimmer, multi-location/single-pole

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CUL, FCC, NOM, ICC, IFTEL