

Eaton PDG2X3TA225

Catalog Number: PDG2X3TA225

Eaton Power Defense molded case circuit breaker accessory terminal, Terminal, Three-pole, AWG 4-4/0, PD2 Global, Power Defense, Frame J-K, Power Defense, Box terminal, Aluminum, Frame 2

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Power Defense terminal	PDG2X3TA225
UPC	Product Length/Depth
786689245887	177.8 mm
Product Height	Product Width
12.7 mm	114.3 mm
Product Weight	Compliances
45.3592 g	Contact Manufacturer

Delivery program

Frame

2

Number of poles

Three-pole

Other

Wire material

Aluminum

Technical information

Wire size

AWG 4-4/0

General information

Circuit breaker type

PD2 Global

Frame size

Frame J-K

Series

Power Defense

Technical data - Mechanical - Terminals

Terminals

Box terminal

Resources

Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

Installation instructions

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

Multimedia

[Power Defense molded case circuit breakers](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense Breakers](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

Specifications and datasheets

[Eaton Specification Sheet - PDG2X3TA225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PDG2X3TA225

Catalog Number: PDG2X3TA225

Eaton Power Defense molded case circuit breaker accessory terminal, Terminal, Three-pole, AWG 4-4/0, PD2 Global, Power Defense, Frame J-K, Power Defense, Box terminal, Aluminum, Frame 2

Photo is representative

General specifications

Product Name	Eaton Power Defense terminal	Catalog Number	PDG2X3TA225
UPC	786689245887	Product Length/Depth	177.8 mm
Product Height	12.7 mm	Product Width	114.3 mm
Product Weight	45.3592 g	Compliances	Contact Manufacturer

Delivery program

Frame

2

Number of poles

Three-pole

Other

Wire material

Aluminum

Technical information

Wire size

AWG 4-4/0

General information

Circuit breaker type

PD2 Global

Frame size

Frame J-K

Series

Power Defense

Technical data - Mechanical - Terminals

Terminals

Box terminal

Resources

Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

Installation instructions

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

Multimedia

[Power Defense molded case circuit breakers](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Eaton Power Defense for superior arc flash safety](#)

[Power Defense Breakers](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

Specifications and datasheets

[Eaton Specification Sheet - PDG2X3TA225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)