



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PFME30LCYUNV166 Indust-Pfme Led Flood 30000 Lumen 100-277 Vac *Crouse-Hinds*

Catalog Number	PFME30LCYUNV166
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Pfme Led Floodlight, Cool White, Dimmable Driver, 750W-1000W Hid Equivalent, 50/60 HZ, Polycarbonate Lens, 30000 Lumens, 127 LM/W, Aluminum, Yoke Mount, Standard 120° Angle, >0.90 PF, 120-277 Vac, 127-400 VDC, 242W
Weight per unit	77.0 (lbs/each)
Product Category	Lighting

Features

dimensions	20.1600 IN X 4.1700 IN X 12.5000 IN
------------	-------------------------------------

Descriptions

Description	INDUST-PFME LED FLOOD 30000 LUMEN 100-277 VAC
extra long description	CRS-H PFME30LCY-UNV1-66 PFME30LCY-U
Features	PFME LED floodlights are certified for use wet locations and are UL Listed and CSA certified. These floodlights are suitable for locations requiring continuous and consistent light levels in extreme ambient temperatures and where wet, dusty, hot and/or cold conditions exist.
Long Description	Eaton Crouse-Hinds series PFME LED floodlight, Cool white, Dimmable driver, 750W-1000W HID equivalent, 50/60 Hz, Polycarbonate lens, 30000 lumens, 127 lm/W, Aluminum, Yoke mount, Standard 120° angle, >0.90 PF, 120-277 Vac, 127-400 Vdc, 242W
Product Type	PFME30LCY-UNV1-66

Manufacturer Information

Brand	Eaton
GTIN	00662276966826
Manufacturers Part Number	PFME30LCY-UNV1-66
UPC	662276966826

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	77



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Lighting and Lighting Controls