

# Eaton PRL1X3225X60CS

Catalog Number: PRL1X3225X60CS

Eaton Pow-R-Xpress PRL1X INTERIOR, 120/208V, 3PH 4W,  
225A, 60 CKT, CU BUS, SHORT INTERIOR

## General specifications



Product Name	Catalog Number
Eaton Pow-R-Xpress PRL1X panelboard	PRL1X3225X60CS
UPC	Product Length/Depth
786689671587	49 in
Product Height	Product Width
6.5 in	8.5 in
Product Weight	Compliances
87 lb	NEMA Compliant
Certifications	
UL 67	

## Physical Attributes

### Bus material

Copper

### Type

PRL1X INTERIOR

## Performance Ratings

### Amperage Rating

225 A

## Resources

### Brochures

[Eaton's Pow-R-Xpress stocking program](#)

[Pow-R-Xpress stocking program flyer](#)

[Pow-R-Xpress quick selector reference guide](#)

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL1X3225X60CS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PRL1X3225X60CS

Catalog Number: PRL1X3225X60CS

Eaton Pow-R-Xpress PRL1X INTERIOR, 120/208V, 3PH 4W, 225A, 60 CKT, CU BUS, SHORT INTERIOR

## General specifications



Product Name	Catalog Number
Eaton Pow-R-Xpress PRL1X panelboard	PRL1X3225X60CS
UPC	Product Length/Depth
786689671587	49 in
Product Height	Product Width
6.5 in	8.5 in
Product Weight	Compliances
87 lb	NEMA Compliant
Certifications	
UL 67	

## Physical Attributes

### Bus material

Copper

### Type

PRL1X INTERIOR

## Performance Ratings

### Amperage Rating

225 A

## Resources

### Brochures

[Eaton's Pow-R-Xpress stocking program](#)

[Pow-R-Xpress stocking program flyer](#)

[Pow-R-Xpress quick selector reference guide](#)

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - PRL1X3225X60CS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)